



- Exhaust air outlet in the ceiling, motor driven exhaust air flap for chamber kiln N 500 E
- Delivery incl. pipe connection for connecting an air outlet with 80 mm diameter for N 140 E - N 280 E
- Delivery incl. 3 ceramic supports and lower shelf for safe stacking of the kiln furniture (models N 140 E - N 280 E)
- Delivery incl. SiC-bottom plate for even stacking of the kiln furniture (chamber kiln N 500 E)
- Delivery incl. base
- Comfortable charging height with base of 800 mm (chamber kiln N 500 E = 500 mm)
- Defined application within the constraints of the operating instructions
- NTLog for Nabertherm Controller: Recording of process data with USB-flash drive
- Controls description see page 30



Model	Tmax °C	Inner dimensions in mm			Volume in l	Outer dimensions in mm			Connected load kW	Electrical connection*	Weight in kg
		w	d	h		W	D	H <sup>1</sup>			
N 140 LE	1100	450 <sup>2</sup>	580	570 <sup>3</sup>	140	720	1130	1440	6.0	1-phase <sup>4</sup>	275
N 210 LE	1100	500 <sup>2</sup>	580	700 <sup>3</sup>	210	770	1130	1570	9.0	3-phase	320
N 280 LE	1100	520 <sup>2</sup>	580	890 <sup>3</sup>	280	790	1130	1760	9.0	3-phase	375
N 140 E	1300	450 <sup>2</sup>	580	570 <sup>3</sup>	140	720	1130	1440	9.0	3-phase	275
N 210 E	1300	500 <sup>2</sup>	580	700 <sup>3</sup>	210	770	1130	1570	11.0	3-phase	320
N 280 E	1300	520 <sup>2</sup>	580	890 <sup>3</sup>	280	790	1130	1760	15.0	3-phase	375
N 500 E	1300	600	820	1000	500	1000	1400	1830	30.0	3-phase	700

<sup>1</sup>Base included

<sup>2</sup>Collar width minus 50 mm

\*Please see page 30 for more information about supply voltage

<sup>3</sup>Collar height minus 110 mm

<sup>4</sup>Fusing of 32 A if connected to 230 V